










1

DETERMINE HANDPIECE APPLICATION
ISO-B 5-Hole
ISO-C 6-Pin
Kinetic-360
Non-Optic 4-Hole

ISO-B 5-Hole Requires #1212 Halogen Lamp Module		→	1211
ISO-B 5-Hole Vari-Lux LED Variable Intensity		→	1260
ISO-C 6-Pin Requires #1242 Halogen Lamp Module		→	1240
Kinetic-360 Requires #1224 Coupling and #1222 Lamp Module		→	1221
Non-Optic 4-Hole Accepts 5-Hole Handpiece Without Light Capability		→	2430

2

CHOOSE TUBING STYLE
Straight Asepsis
Coiled Asepsis
Straight Euro
Straight KINC

Straight Wired		→	S
Coiled Wired		→	C
Straight Euro		→	U
Straight KINC		→	K

3

CHOOSE TUBING COLOR
Gray, Light Gray,
Black, Sand, Surf
or Shadow

Gray Color Tubing	→	Y
Light Gray Color Tubing	→	T
Black Color Tubing	→	K
Sand Color Tubing	→	D
Surf Color Tubing	→	F
Shadow Color Tubing	→	W

4

CHOOSE H/P NUT COLOR
Stainless Steel
Gray, Sand or
Black Color Delrin

Stainless Steel H/P Nut	→	S
Gray Color H/P Nut	→	Y
Sand Color H/P Nut	→	D
Black Color H/P Nut	→	K

5

CONSTRUCT PRODUCT DESIGNATION
Use codes from
steps 1-4 added
together

1 + 2 + 3 + 4